



The manufacturer
may use the mark:



Revision 1.1 August 2, 2023
Surveillance Audit Due
August 1, 2026



Certificate / Certificat Zertifikat / 合格証

VIN 2102101 C001

exida hereby confirms that the:

Floating Ball Valves

Vinco Valves
Vila Nova Famalicão, Portugal

Have been assessed per the relevant requirements of:

IEC 61508 : 2010 Parts 1-2

and meets requirements providing a level of integrity to:

Systematic Capability: SC 3 (SIL 3 Capable)

Random Capability: Type A, Route 2_H Device

**PFH/PFD_{avg} and Architecture Constraints
must be verified for each application**

Safety Function:

The Ball Valve will move to the designed safe position per the actuator design within the specified safety time.

Application Restrictions:

The unit must be properly designed into a Safety Instrumented Function per the Safety Manual requirements.



Evaluating Assessor

Certifying Assessor

VIN 2102101 C001

Systematic Capability: SC 3 (SIL 3 Capable)**Random Capability: Type A, Route 2_H Device****PFH/PFD_{avg} and Architecture Constraints
must be verified for each application****Systematic Capability :**

These products have met manufacturer design process requirements of Safety Integrity Level (SIL) 3. These are intended to achieve sufficient integrity against systematic errors of design by the manufacturer.

A Safety Instrumented Function (SIF) designed with this product must not be used at a SIL level higher than stated.

Random Capability:

The SIL limit imposed by the Architectural Constraints must be met for each element. This device meets *exida* criteria for Route 2_H.

Versions:

Soft Seated Valve Models: SF, SFH, XF, XFH, VF, VFH, RP, XP, LP, DF, DFH, HF, HFH, BF, BFH, CF, CFH, GFH, HFH7

Metal Seated Valve Models: CFM, XFM, BFM, SFM

Cryogenic Valves Models: CXF, CCF, CBF

IEC 61508 Failure Rates in FIT¹ Static Applications

Application/Device/Configuration	λ_{SD}	λ_{SU}	λ_{DD}	λ_{DU}
Full Stroke, Clean Service	0	0	0	443
Tight Shut-Off, Clean Service	0	0	0	1182
Open on Trip, Clean Service	0	161	0	282
Full Stroke, Severe Service	0	0	0	767
Tight Shut-Off, Severe Service	0	0	0	2243
Open on Trip, Severe Service	0	307	0	460

¹FIT – 1 failure/10⁹ hours

SIL Verification:

The Safety Integrity Level (SIL) of an entire Safety Instrumented Function (SIF) must be verified via a calculation of PFH/PFD_{avg} considering redundant architectures, proof test interval, proof test effectiveness, any automatic diagnostics, average repair time and the specific failure rates of all products included in the SIF. Each element must be checked to assure compliance with minimum hardware fault tolerance (HFT) requirements.

The following documents are a mandatory part of certification:

Assessment Report: VIN 21/02-101 R001 V2R1 (or later)

Safety Manual: Vinco Valves Safety SIL Ball Valves V1R0 (or later)

Floating Ball Valves



80 N Main St
Sellersville, PA 18960